













## Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – ENCLOSED AND GASKETED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE – Plantweb™ Insight CONNECTED LIGHTING</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: UP TO 5,500 OR UP TO 9,500 OR UP TO 17,500</li> <li>• COLOR TEMPERATURE: 3000K OR 3500K OR 4000K OR 4500K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: CID2, CIID2   CIII   CI, ZONE 2   CII, ZONE 22 -- IECEx/ATEX: STANDARD MODEL: ZONE 2 and 21/22</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 46W – 145W</li> <li>• EFFICACY: UP TO 149 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40 °C to +65 °C (-40 °F to +149 °F)</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, STAINLESS STEEL WIRE GLOBE GUARD, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE I, III, V, V WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• MGC – APPLETON MERCMASTER CONNECT LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Mercmaster Connect LED Luminaires</a></p> 
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,500 OR 5,500 OR 7,500 OR 9,500 OR 11,500 OR 14,500 OR 17,500 OR 20,000 OR 24,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 or 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: STANDARD MODEL: CID2   CIID1, CIID2   CIII   CI, ZONE 2   ZONE 21 -- IECEx/ATEX: STANDARD MODEL: ZONE 2 and 21/22</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 3,500 OR 5,500 LUMENS, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 30W – 210W</li> <li>• EFFICACY: UP TO 149 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, HIGH TEMP UP TO +75°C (+167°F), -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE I, III, V, V WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• MLG – APPLETON MERCMASTER LED GENERATION 3 SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Mercmaster LED Generation 3 Series Luminaires</a></p> 



# Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – ENCLOSED AND GASKETED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,300 OR 4,400 OR 5,500</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 or 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: CID2   CI, ZONE 2   ZONE 21   CI, ZONE 2   CIID1   ZONE 20   CIID2   CIII -- IECECx/ATEX: ZONE 2 AND 21/22</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 28W – 48W</li> <li>• EFFICACY: UP TO 118 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40° C TO +65° C (-40°F TO +149° F) STANDARD, -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• MLLED – APPLETON MERCMASTER LED LOW PROFILE SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Mercmaster LED Low Profile Series Luminares</a></p> <div style="text-align: center;">  </div>
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,300 OR 4,400 OR 5,500</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 or 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING – DIRECT RETROFIT FOR CROUSE-HINDS CHAMP SERIES</li> <li>• CERTIFICATION: NEC/CEC: CID2   CI, ZONE 2   CIID1   ZONE 21   CIID2   CIII</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 28W – 48W</li> <li>• EFFICACY: UP TO 118 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40° C TO +65° C (-40°F TO +149° F)</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• VMV – APPLETON CONTENDER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Contender LED Series Luminares</a></p> <div style="text-align: center;">  </div>





## Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – ENCLOSED AND GASKETED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA/LINEAR FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 4,300 OR 7,600</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: CID2   CIID1   CIID2   CIII   CI, ZONE 2   CII, ZONE 20   CII, ZONE 21</li> <li>• CONSTRUCTION: LINEAR INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, 10G VIBRATION RATING</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 33W – 55W</li> <li>• EFFICACY: UP TO 139 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: CLEAR OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: LINEAR PATTERN</li> </ul>	<ul style="list-style-type: none"> <li>• RM – APPLETON RIGMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Rigmaster LED Linear Series Luminaires</a></p> 
<p><b>LED HIGH BAY FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 9,500 OR 15,000 OR 19,500 OR 24,000 OR 30,000 OR 38,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: CID2   CIID1   CIID2   CIII   ZONE 20, 21, 22   CI, ZONE 2 -- ATEX/IECEX: ZONE 2, 21, 22   CE   UKCA</li> <li>• CONSTRUCTION: SQUARE INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, THREE 3/4" NPT RIGID CONDUIT ENTRIES, OPTIONAL M20 METRIC ADAPTERS AVAILABLE, 10G VIBRATION RATING (BLLL AND BHLL MODELS)</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 73W – 317W</li> <li>• EFFICACY: UP TO 141 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -40°C TO +55°C (-40°F TO +131°F) FOR BHLL3 OUTPUT</li> <li>• OPTIONS: FIELD REPLACEABLE CLEAR OR FROSTED GLASS LENS OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL WIRE LENS GUARD, VISOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER, FUSING</li> <li>• DISTRIBUTION: AISLE, VERY NARROW, NARROW, MEDIUM, WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• BLL OR BHL – APPLETON BAYMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Baymaster LED Luminaire</a></p> 





## Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – ENCLOSED AND GASKETED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED FLOOD FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 9,500 OR 15,000 OR 19,500 OR 24,000 OR 30,000 OR 38,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC: CID2   CIID1   CIID2   CIII   ZONE 20, 21, 22   CI, ZONE 2 -- ATEX/IECEX: ZONE 2, 21, 22   CE   UKCA</li> <li>• CONSTRUCTION: SQUARE INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, ARCHITECTURAL BRONZE POLYESTER CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, THREE 3/4" NPT RIGID CONDUIT ENTRIES, OPTIONAL M20 METRIC ADAPTERS AVAILABLE, 10G VIBRATION RATING</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 73W – 317W</li> <li>• EFFICACY: UP TO 141 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -40°C TO +55°C (-40°F TO +131°F) FOR AMLHL3 OUTPUT</li> <li>• OPTIONS: FIELD REPLACEABLE CLEAR OR FROSTED GLASS LENS OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL WIRE LENS GUARD, VISOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER, FUSING</li> <li>• DISTRIBUTION: 3X3, 5X5, 7X6, 7X7</li> </ul>	<ul style="list-style-type: none"> <li>• AMLG OR AMLH – APPLETON AREAMASTER GENERATION 2 LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Areamaster Generation 2 LED Luminaires</a></p> 





# Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – EXPLOSIONPROOF AND DUST-IGNITIONPROOF LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,700 OR 5,400 OR 7,900 OR 10,000 OR 11,600 OR 13,600 OR 16,700 OR 19,300</li> <li>• COLOR TEMPERATURE: 5000K OR 4000K OR 3000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING</li> <li>• CERTIFICATION: EXPLOSIONPROOF, DUST-IGNITIONPROOF - NEC/CEC: CID1, CID2   CI, ZONE 1   CIID1   CIID2   CIII</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, APPROVED FOR USE IN PAINT SPRAY BOOTHS, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 30W – 161W</li> <li>• EFFICACY: UP TO 132 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F)</li> <li>• OPTIONS: CLEAR OR DIFFUSED GLASS GLOBE, STAINLESS STEEL WIRE GLOBE GUARD, STAINLESS STEEL SAFETY CABLE, FUSING</li> <li>• DISTRIBUTION: TYPE V SYMMETRICAL, V WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• CMLED – APPLETON CODEMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Code•Master LED Factory Sealed Luminares</a></p> <div style="text-align: center;">  </div>
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 1,600 OR 3,000 OR 5,150</li> <li>• COLOR TEMPERATURE: 5000K OR 3000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING</li> <li>• CERTIFICATION: EXPLOSIONPROOF, DUST-IGNITIONPROOF - NEC/CEC: CID1   CIID1   CIII   ZONE 1</li> <li>• CONSTRUCTION: ROUND TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, SUITABLE FOR USE IN PAINT SPRAY BOOTHS, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 13W – 49W</li> <li>• EFFICACY: UP TO 123 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +55°C (-40°F TO +131°F), -40°C TO +40°C (-40°F TO +104°F) FOR CJLL3 OUTPUT</li> <li>• OPTIONS: REFLECTOR OR DOME, STAINLESS STEEL SAFETY CABLE, ALUMINUM GLOBE GUARD</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• CMLED – APPLETON CODEMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Code•Master Jr. LED Factory Sealed Luminares</a></p> <div style="text-align: center;">  </div>





# Appleton™ LED Lighting Specification

HAZARDOUS LOCATION RATED – EXPLOSIONPROOF, DUST-IGNITIONPROOF LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 1,700 OR 3,200</li> <li>• COLOR TEMPERATURE: 5000K OR 3000K</li> <li>• CRI: 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR MOUNTING OPTIONS</li> <li>• CERTIFICATION: EXPLOSIONPROOF, DUST-IGNITIONPROOF - NEC/CEC: CID1   CIID1   CIII</li> <li>• CONSTRUCTION: ROUND TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 13W – 27W</li> <li>• EFFICACY: UP TO 134 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 100-300 VDC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -25 °C TO +55 °C (-13 °F TO +131 °F)</li> <li>• OPTIONS: REFLECTORS, GLOBE GUARD</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• AAL OR AL – APPLETON A-51 LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton A-51 LED Factory Sealed Luminaires</a></p> 
<p><b>LED TASK/AREA/LINEAR FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 4,300 OR 7,600</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: EXPLOSIONPROOF, DUST-IGNITIONPROOF - NEC/CEC: CID1   CIID1   CIII   CI, ZONE 1</li> <li>• CONSTRUCTION: LINEAR TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, 4G VIBRATION RATING</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 33W – 55W</li> <li>• EFFICACY: UP TO 137 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 100-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: CLEAR OR FROSTED GLASS, STAINLESS STEEL SAFETY CABLE</li> <li>• DISTRIBUTION: LINEAR PATTERN</li> </ul>	<ul style="list-style-type: none"> <li>• ERM – APPLETON EXPLOSIONPROOF RIGMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Explosionproof Rigmaster LED Linear Series Luminaires</a></p> 

## Appleton™ LED Lighting Specification





HAZARDOUS LOCATION RATED - EXIT AND EMERGENCY LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED EXIT SIGN</b></p> <ul style="list-style-type: none"> <li>• MOUNTING: WALL MOUNT OR CEILING MOUNT OR PENDANT MOUNT. SEE LIGHTING PLANS FOR MOUNTING HEIGHT.</li> <li>• CERTIFICATION: NEC: CID2   CI, ZONE 2</li> <li>• CONSTRUCTION: FIBERGLASS REINFORCED POLYCARBONATE HOUSING, UV STABILIZED POLYCARBONATE LENS, STAINLESS STEEL SCREWS, DIE-CAST ALUMINUM MOUNTING BRACKET, 1/2" NPT ENTRY HUB ON TOP, NICKEL CADMIUM BATTERY, SINGLE OR DOUBLE SIDED, RED OR GREEN TEXT, FIELD REMOVEABLE DIRECTIONAL ARROWS, SELF DIAGNOSTIC TESTING SYSTEM, LED INDICATOR LIGHT, IP66, CORROSION RESISTANT, SUITABLE FOR USE IN WET LOCATIONS</li> <li>• BATTERY BACKUP: YES, 90 MINUTE RUN TIME, 4.8V RECHARGEABLE NICKEL CADMIUM BATTERY</li> <li>• WATTAGE: 3W</li> <li>• VOLTAGE: 120 VAC / 277 VAC</li> <li>• CONFIGURATION: SINGLE SIDED OR DOUBLE SIDED, GREEN OR RED</li> <li>• SURGE PROTECTION: 6KV, 120 VAC OR 277 VAC</li> <li>• AMBIENT TEMPERATURE: -20°C TO +50°C (-4°F TO +122°F)</li> <li>• OPTIONS: REPLACEMENT BATTERY PACK, FACE PLATE, BACK PLATE, LENS, MAGNET (TESTING), SURGE PROTECTION, TAMPER PROOF SCREWS</li> </ul>	<ul style="list-style-type: none"> <li>• HEX – APPLETON HEX SERIES LED EXIT SIGN</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton HEX Series LED Hazardous Location Exit Sign</a></p> <div style="text-align: center;">  </div>
<p><b>LED EMERGENCY EGRESS LIGHTING SYSTEM WITH REMOTE OR DIRECT MOUNTED LAMPS</b></p> <ul style="list-style-type: none"> <li>• MOUNTING: WALL MOUNTED. SEE LIGHTING PLANS FOR MOUNTING HEIGHT.</li> <li>• CERTIFICATION: NEC: CID2   CI, ZONE 2</li> <li>• CONSTRUCTION: FIBERGLASS REINFORCED POLYESTER HOUSING, SILICONE GASKET, NICKEL PLATED BRASS ENTRY HUB, STAINLESS STEEL COVER SCREWS, ALUMINUM LAMPHEADS, SELF DIAGNOSTIC TESTING SYSTEM, LED INDICATOR LIGHT, TYPE 4X, IP66, RAIN TIGHT SUITED FOR OPERATION IN HIGHLY CORROSIVE AND WET LOCATIONS</li> <li>• BATTERY BACKUP: YES, 90 OR 180 MINUTE RUN TIME, NICKEL CADMIUM BATTERY, SYSTEM SUPPORTS 4 LIGHT HEADS (AT 1.5W EACH) IN ANY MAIN/REMOTE COMBINATION UTILIZING UP TO 6W OF OUTPUT POWER</li> <li>• WATTAGE: 1.5W – 6W</li> <li>• VOLTAGE: 120-277 VAC</li> <li>• AMBIENT TEMPERATURE: 0°C TO +55°C (+32°F TO +131°F)</li> <li>• OPTIONS: REPLACEMENT LAMP KIT, BATTERY PACK KIT, CIRCUIT CHARGER BOARD KIT, NICKEL PLATED BRASS M25 MALE, 3/4" NPT FEMALE HUB</li> </ul>	<ul style="list-style-type: none"> <li>• APPLETON N2LED SERIES EMERGENCY LUMINAIRES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton N2LED Series Emergency Luminaires</a></p> <div style="text-align: center;">  </div>

# Appleton™ LED Lighting Specification





ORDINARY LOCATION RATED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE – Plantweb™ Insight CONNECTED LIGHTING</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: UP TO 5,500 OR UP TO 9,500 OR UP TO 17,500</li> <li>• COLOR TEMPERATURE: 3000K OR 3500K OR 4000K OR 4500K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 46W – 145W</li> <li>• EFFICACY: UP TO 149 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40 °C to +65 °C (-40 °F to +149 °F)</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, STAINLESS STEEL WIRE GLOBE GUARD, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE I, III, V, V WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• IMGC – APPLETON INDUSTRIAL MERCMaster CONNECT LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Industrial Mercmaster Connect LED Luminaires</a></p> 
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,500 OR 5,500 OR 7,500 OR 9,500 OR 11,500 OR 14,500 OR 17,500 OR 20,000 OR 24,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, NOM, IECEE CB</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 3,500 OR 5,500 LUMENS, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 30W – 210W</li> <li>• EFFICACY: UP TO 149 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, HIGH TEMP UP TO +75°C (+167°F), -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE I, III, V, V WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• IMLG – APPLETON INDUSTRIAL MERCMaster LED GENERATION 3 SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Industrial Mercmaster LED Generation 3 Series Luminaires</a></p> 






# Appleton™ LED Lighting Specification

ORDINARY LOCATION RATED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,300 OR 4,400 OR 5,500</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, NOM, IECEE CB</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 28W – 48W</li> <li>• EFFICACY: UP TO 118 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• IMLLED – APPLETON INDUSTRIAL MERCMASTER LED LOW PROFILE SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Industrial Mercmaster LED Low Profile Series Luminaires</a></p> <div style="text-align: center;">  </div>
<p><b>LED TASK/AREA FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 3,300 OR 4,400 OR 5,500</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING – DIRECT RETROFIT FOR CROUSE-HINDS CHAMP SERIES</li> <li>• CERTIFICATION: NEC/CEC</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 28W – 48W</li> <li>• EFFICACY: UP TO 118 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F)</li> <li>• OPTIONS: FIELD REPLACEABLE POLYCARBONATE OR GLASS GLOBE, OR GLASS PRISMATIC REFRACTOR, STAINLESS STEEL WIRE GLOBE GUARD, DARK SKY VISOR, REFLECTOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: TYPE V</li> </ul>	<ul style="list-style-type: none"> <li>• IVMV – APPLETON INDUSTRIAL CONTENDER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Industrial Contender LED Series Luminaires</a></p> <div style="text-align: center;">  </div>

# Appleton™ LED Lighting Specification

ORDINARY LOCATION RATED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED TASK/AREA/LINEAR FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 4,300 OR 7,600</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, NOM</li> <li>• CONSTRUCTION: LINEAR INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, 10G VIBRATION RATING</li> <li>• BATTERY BACKUP: YES, 120-277 VAC, 90 OR 180 MINUTE RUNTIME</li> <li>• WATTAGE: 33W – 55W</li> <li>• EFFICACY: UP TO 139 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -20°C TO +55°C (-4°F TO +131°F) EMERGENCY</li> <li>• OPTIONS: CLEAR OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: LINEAR PATTERN</li> </ul>	<ul style="list-style-type: none"> <li>• IRM – APPLETON INDUSTRIAL RIGMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Industrial Rigmaster LED Linear Series Luminaires</a></p> <div style="text-align: center;">  </div>
<p><b>LED HIGH BAY FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 9,500 OR 15,000 OR 19,500 OR 24,000 OR 30,000 OR 38,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, NOM, IECEE CB, CE, UKCA</li> <li>• CONSTRUCTION: SQUARE INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, THREE 3/4" NPT RIGID CONDUIT ENTRIES, OPTIONAL M20 METRIC ADAPTERS AVAILABLE, 10G VIBRATION RATING (IBLL AND IBHL MODELS)</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 73W – 317W</li> <li>• EFFICACY: UP TO 141 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -40°C TO +55°C (-40°F TO +131°F) FOR IBHLL3 OUTPUT</li> <li>• OPTIONS: FIELD REPLACEABLE CLEAR OR FROSTED GLASS LENS OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL WIRE LENS GUARD, VISOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER, FUSING</li> <li>• DISTRIBUTION: AISLE, VERY NARROW, NARROW, MEDIUM, WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• IBLL OR IBHL – APPLETON INDUSTRIAL BAYMASTER LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p style="text-align: center;"><a href="#">Appleton Industrial Baymaster LED Luminaire</a></p> <div style="text-align: center;">  </div>

# Appleton™ LED Lighting Specification

ORDINARY LOCATION RATED LUMINAIRES			
DESCRIPTION	MANUFACTURER	PRODUCT IMAGE	URL / QR
<p><b>LED HIGH BAY FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 50,000 OR 60,000 OR 75,000 OR 90,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, IECEE CB, CE, UKCA</li> <li>• CONSTRUCTION: ROUND INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66, GRAY EPOXY POWDER COAT CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, FOUR 3/4" NPT RIGID CONDUIT ENTRIES, OPTIONAL M20 METRIC ADAPTERS AVAILABLE, 3G VIBRATION RATING</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 360W – 640W</li> <li>• EFFICACY: UP TO 146 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 277-480 VAC</li> <li>• DIMMING: 0-10VDC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OR 20KV/10KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +75°C (-40°F TO +167°F) FOR IHC*5, -40°C TO +70°C (-40°F TO +158°F) FOR IHC*6 AND IHC*7, -40°C TO +65°C (-40°F TO +149°F) FOR IHC*9</li> <li>• OPTIONS: PRE-WIRED, 5 PIN NEMA SOCKET FOR PHOTOCONTROL, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER</li> <li>• DISTRIBUTION: VERY NARROW, NARROW, MEDIUM, VERY WIDE</li> </ul>	<ul style="list-style-type: none"> <li>• IHC – APPLETON IHC LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton IHC LED Luminaire</a></p> 
<p><b>LED FLOOD FIXTURE</b></p> <ul style="list-style-type: none"> <li>• LUMEN OUTPUT: 9,500 OR 15,000 OR 19,500 OR 24,000 OR 30,000 OR 38,000</li> <li>• COLOR TEMPERATURE: 3000K OR 4000K OR 5000K</li> <li>• CRI: 70 OR 80</li> <li>• MOUNTING: SEE LIGHTING PLANS FOR MOUNTING AND MANUFACTURER CATALOG PAGES FOR OPTIONS</li> <li>• CERTIFICATION: NEC/CEC, NOM, IECEE CB, CE, UKCA</li> <li>• CONSTRUCTION: SQUARE INDUSTRIAL TYPE FIXTURE, COPPERFREE ALUMINUM HOUSING WITH SILICONE RUBBER GASKET SUITABLE FOR WET LOCATIONS, TYPE 3R, 4, 4X, IP66/67, ARCHITECTURAL BRONZE POLYESTER CORROSION RESISTANT FINISH, STAINLESS STEEL HARDWARE, THREE 3/4" NPT RIGID CONDUIT ENTRIES, OPTIONAL M20 METRIC ADAPTERS AVAILABLE, 10G VIBRATION RATING</li> <li>• BATTERY BACKUP: NO</li> <li>• WATTAGE: 73W – 317W</li> <li>• EFFICACY: UP TO 141 LM/W</li> <li>• VOLTAGE: 120-277 VAC, 125-300 VDC OR 347-480 VAC</li> <li>• SURGE PROTECTION: 6KV/3KA STANDARD, 10KV/5KA OPTIONAL</li> <li>• AMBIENT TEMPERATURE: -40°C TO +65°C (-40°F TO +149°F) STANDARD, -40°C TO +55°C (-40°F TO +131°F) FOR IAMLHL3 OUTPUT</li> <li>• OPTIONS: FIELD REPLACEABLE CLEAR OR FROSTED GLASS LENS OR DIFFUSED POLYCARBONATE LENS, STAINLESS STEEL WIRE LENS GUARD, VISOR, STAINLESS STEEL SAFETY CABLE, REPLACEABLE DRIVER, FUSING</li> <li>• DISTRIBUTION: 3X3, 5X5, 7X6, 7X7</li> </ul>	<ul style="list-style-type: none"> <li>• IAMLG OR IAMLH – APPLETON INDUSTRIAL AREAMASTER GENERATION 2 LED SERIES</li> <li>• OR EQUAL</li> </ul>		<p><a href="#">Appleton Industrial Areamaster Generation 2 LED Luminaires</a></p> 